

EA620TB- 16~ - 104  
(パンチ・ダイセット)

	サイズ (表示刻印)	パンチ穴径	電線管外径	セットホルト	指定下穴径
TB - 16	B16 (1/2 ")	21.8mm	21.0mm	3/8 "24山	ドリル 11mm
TB - 22	B22 (3/4 ")	27.6mm	26.5mm	3/4 "16山	11ドリル穴を開け後B16パンチを用いる。
TB - 28	B28 (1")	34.1mm	33.3mm	"	"
TB - 36	B36 (1 1/4 ")	42.7mm	41.9mm	"	"
TB - 42	B42 (1 1/2 ")	48.7mm	47.8mm	"	"
TB - 54	B54 (2")	60.5mm	59.6mm	"	"
TB - 70	B70 (2 1/2 ")	76.1mm	75.2mm	"	"
TB - 82	B82 (3")	88.9mm	87.9mm	"	"
TB - 92	B92 (3 1/2 ")	102.8mm	100.7mm	"	"
TB - 104	B104 (4")	115.5mm	113.4mm	"	"

工具鋼製  
EA620TBとの併用

