

サンスーパーSロープ(Sun Super S Rope)

原料: ポリエチレン モノフィラメント 高強力糸
比重: 0.95

寸 法		引 張 強 度				標準質量 (kg/200m)			
直 径	周 径	NK 規格		当社規格 (標準)		NK 規格	三つ打ち (普通打)	三つ打ち (硬打)	クロス
mm	inch	kN	tf	kN	tf				
6	3/4			6.35	0.65	11.0	3.63	3.74	6.45 8.16
7	7/8			8.50	0.87		4.94	5.09	
8	1			11.0	1.12		6.45	6.64	
9	1 1/8			13.7	1.40		8.16	8.41	
10	1 1/4	12.7	1.30	16.8	1.71		10.1	10.4	
11	1 3/8			20.1	2.05	15.0 21.0 27.0	12.2	12.6	12.2
12	1 1/2	17.7	1.80	23.6	2.41		14.5	14.9	14.5
14	1 3/4	23.5	2.40	31.8	3.24		19.8	20.3	19.8
16	2	29.4	3.00	40.9	4.17		25.8	26.6	25.8
18	2 1/4	37.7	3.84	51.2	5.22		34.0	32.7	33.6
20	2 1/2	44.1	4.50	62.5	6.37	42.0	40.3	41.5	40.3
22	2 3/4	54.9	5.60	74.9	7.64	50.0	48.8	50.2	48.8
24	3	63.7	6.50	88.4	9.01	60.0	58.1	59.8	58.1
26	3 1/4	73.5	7.50	103	10.5	70.0	68.1	70.2	68.1
28	3 1/2	83.4	8.50	119	12.1	81.0	79.0	81.4	79.0
30	3 3/4	97.1	9.90	135	13.8	93.0	90.7	93.4	90.7
32	4	108	11.0	153	15.6	105	103	106	103
34	4 1/4			171	17.5		117	120	117
35	4 3/8	127	13.0	181	18.5	126	123	127	123
36	4 1/2			191	19.5		131	135	131
38	4 3/4			212	21.6	164 208	146	150	146
40	5	164	16.7	233	23.8		161	166	161
42	5 1/4			256	26.1		178	183	178
45	5 5/8	203	20.7	292	29.8		204	210	204
48	6			330	33.6		232	239	232
50	6 1/4	250	25.5	356	36.3	257	252	260	252
55	6 7/8	294	30.0	428	43.6	310	305	314	305
60	7 1/2	348	35.5	504	51.4	370	363	374	363
65	8	402	41.0	586	59.8	434	426	439	426
70	8 11/16	461	47.0	676	68.9	501	494	509	494
75	9 1/4	525	53.5	770	78.5	577	567	584	567
80	9 7/8	593	60.5	871	88.8	657	645	664	645
85	10 1/2	667	68.0	977	99.6	744	728	750	728
90	11 1/8	735	75.0	1090	111	834	816	841	816
95	11 3/4	814	83.0	1210	123	930	910	937	910
100	12 3/8	897	91.5	1330	136	1030	1010	1040	1010
110	13 5/8			1590	163		1220	1260	1220
120	14 7/8			1880	192		1450	1500	1450

- (注) 1. 引張強度及び伸度は乾、湿共変化ありません。
2. 切断時の伸度は25～30%です。
3. 引張強度は35℃の状態における測定値です。