


NR 端子(片押しタイプ)



Y-151

寸法表

(寸法には、多少の誤差があります。)

	ロープ径	L	D	d	A	B	t
NRI C=φ4.0 鉄(SWRM) ユニクロ	1.0	20	9	5.2	10	2.5	1.2
	1.0	20	8.5	3.2	10	3.7	1.2
	1.2	20	8.5	4.2	10	3	1.2
	1.5	20	8.5	5.2	10	2.5	1.2
NRS C=φ4.0 ステンレス (SUS304)	1.0	20	8.5	4.2	10	3	1.2
	1.0	20	9.5	5.2	10	2.5	1.1
	1.2	20	8.5	4.2	10	3.5	1.2
	1.2	21	9	3.2	10	3	1.2
	1.5	20	9	4.2	10	3	1.2
	1.5	20	9.5	5.2	10	2.5	1.1

EA628ST-1.-2.-3
EA628ST-11.-12.-13
EA628ST-21.-22.-23