

クレモナSロープ(Kuralon S Rope)

原料: ポリエステル混紡ビニロン 紡績糸
比重: 1.33

寸 法		最低引張強度				標準質量（kg／200m）			
直 径	周 径	NK 規格		当社規格		NK 規格	三つ打ち （普通打）	三つ打ち （硬打）	クロス
mm	inch	kN	tf	kN	tf				
3	3/8			1.18	0.12		1.13	1.16	
4	1/2			2.06	0.21		2.02	2.08	
5	5/8			3.04	0.31		3.15	3.24	
6	3/4			4.31	0.44		4.54	4.68	
7	7/8			5.79	0.59		6.17	6.36	
8	1			7.35	0.75		8.06	8.30	8.30
9	1 1/8			9.22	0.94		10.2	10.5	10.5
10	1 1/4			11.4	1.16		12.5	12.9	12.9
11	1 3/8			13.7	1.40		15.1	15.6	15.6
12	1 1/2			15.6	1.59		18.0	18.5	18.5
14	1 3/4			20.7	2.11		24.5	25.2	25.2
16	2			26.5	2.70		32.0	33.0	33.0
18	2 1/4			33.0	3.36		40.5	41.7	41.7
20	2 1/2			40.0	4.08		50.0	51.5	50.0
22	2 3/4			49.2	5.02		60.5	62.3	60.5
24	3			57.9	5.90		72.0	74.2	72.0
26	3 1/4			67.1	6.84		84.5	87.0	84.5
28	3 1/2			77.0	7.85		98.0	101	98.0
30	3 3/4			87.5	8.92		112	115	112
32	4			98.1	10.0		127	131	127
34	4 1/4			110	11.2		144	148	144
35	4 3/8			117	11.9		153	158	153
36	4 1/2			123	12.5		161	166	161
38	4 3/4			135	13.8		180	185	180
40	5			149	15.2		199	205	199
42	5 1/4			163	16.6		220	227	220
45	5 5/8			185	18.9		252	260	252
48	6			209	21.3		287	296	287
50	6 1/4			225	22.9		311	320	311
55	6 7/8			269	27.4		375	386	375
60	7 1/2			315	32.1		446	459	446
65	8			366	37.3		524	540	524
70	8 11/16			419	42.7		608	626	608
75	9 1/4			477	48.6		698	719	698
80	9 7/8			536	54.7		794	818	794
85	10 1/2			600	61.2		896	923	896
90	11 1/8			667	68.0		1000	1030	1000
95	11 3/4			737	75.2		1120	1150	1120
100	12 3/8			811	82.7		1240	1280	1240
110	13 5/8			967	98.6		1500	1550	1500
120	14 7/8			1140	116		1790	1840	1790

(注) 1. 湿潤時の強度は乾時の約90%です。
2. 伸度は乾時25~30%、湿潤時30~35%です。