





枠式ターンバックル (フック&フック)

Turnbuckle, frame type Hook/Hook



材質：ステンレス SUS304

(mm)

品番	L	W	A	B	S	L ₁	L ₂	捻径	weight (g)	参考使用荷重 (kgf)	(kN)	EA品番	コード No.
TB-4H	57	13	28	50	6	92	128	W-3/16	27	40	0.39	EA638CE-4A	378
TB-5H	70	14	35	60	7	115	160	W-3/16	41	50	0.49	EA638CE-5A	379
TB-6H	90	19	45	75	9	141	200	W-1/4	96	80	0.78	EA638CE-6A	380
TB-8H	120	21	60	100	10	180	260	W-5/16	180	120	1.18	EA638CE-8A	381
TB-9H	150	26	75	120	13	230	330	W-3/8	300	160	1.57	EA638CE-9A	382
TB-12H	200	34	100	156	17	290	440	W-1/2	640	400	3.92	EA638CE-12A	383