







枠式ターンバックル 外れ止め付 (フック&フック)

Turnbuckle, frame type w/stopper Hook/Hook

〈フック部分拡大〉



材質：ステンレス SUS304

(mm)

品番	L	W	A	B	R	L ₁	L ₂	捻径	weight (g)	参考使用荷重		EA品番	コード No.
										(kgf)	(kN)		
TB-6HK	90	19	48	81	2.5	155	213	W-1/4	100	80	0.78	EA638CF-6A	1352
TB-8HK	120	21	65	105	2.5	210	290	W-5/16	150	120	1.18	EA638CF-8A	1353
TB-9HK	150	26	81.5	130	4	250	356	W-3/8	310	160	1.57	EA638CF-9A	1354
TB-12HK	200	34	100	166	6	330	460	W-1/2	680	400	3.92	EA638CF-12A	1355

従来の枠式ターンバックル
(フック&フック)
の外れ止め付きです。

※六角ナット付