




# 楕円リンク

Oval Link

材質：ステンレス SUS304

(mm)



品番	D	P	W	weight (g)	参考使用荷重		EA品番	コード No.
					(kgf)	(kN)		
RO-3	3	19	6	3	70	0.69	EA638DN-16	1879
RO-4	4	26	12	8	90	0.88	EA638DN-17	1880
RO-5	5	28	16	14	150	1.47	EA638DN-18	1881
RO-6	6	31	18	23	250	2.45	EA638DN-19	1882
RO-8	8	50	30	62	350	3.43	EA638DN-20	1883
RO-10	10	60	40	122	600	5.88	EA638DN-22	1885
RO-11	11	70	45	167	650	6.37	EA638DN-23	1886