

Artikel-Nr.	WLL [t]	b1 [mm]	d1 [mm]	d2 [mm]	d3 [mm]	h1 [mm]	Gewicht [kg/100 Stk]
EA638GJ-51	0,16	8	4	8	M4	30	1,10
EA638GJ-52	0,25	10	5	10	M5	37	2,20
EA638GJ-53	0,38	12	6	12	M6	45	3,60
EA638GJ-54	0,63	16	8	16	M8	60	8,40
EA638GJ-55	1,00	20	10	19	M10	75	18,60
EA638GJ-56	1,50	25	12	24	M12	90	25,40

