



Artikel-Nr.		Seil-Ø [mm]	a [mm]	b [mm]	c [mm]	l [mm]	p [mm]	s [mm]	Gewicht [kg/100 Stk]
19000300	-3	2,5	3	4,0	10	21,5	2,0	0,5	0,13
19000350*		3,0	4	5,5	11	23,5	2,8	1,0	0,35
19000400	-4	3,5	4	5,5	12	26,5	3,0	1,0	0,43
19000500	-5	4,0	5	6,5	13	28,5	3,5	1,0	0,69
19000600	-6	5,0	6	8,0	14	30,0	4,0	1,0	0,80
19000700	-7	6,0	7	9,0	15	33,0	4,5	1,0	1,01
19000800	-8	7,0	8	10,0	16	35,0	5,2	1,2	1,01
19000900	-9	8,0	9	11,5	18	39,0	5,7	1,2	1,60
19001000	-10	9,0	10	12,5	20	43,0	6,5	1,5	1,98
19001100	-11	10,0	11	14,0	22	47,5	7,0	1,5	2,95
19001200*	-12	11,0	12,0	15,0	24	51,0	7,5	1,5	3,70
19001300*	-13	12,0	13,0	16,6	26	56,0	8,3	1,8	5,25
19001400*	-14	13,0	14,0	19,0	28	61,0	9,8	2,5	7,25
19001600*	-16	15,0	16,0	22,0	32	69,0	11,2	3,0	8,33
19001800*	-19	16,0	19,0	25,0	35	78,0	12,9	3,0	17,90