



ロングアイボルト

Long Eye Bolt (welded) w/washer and nut

〈ミリネジ〉 Metric Thread 材質：ステンレス SUS304

(mm)

品番	D	L	H	B	T	捻径	weight (g)	参考使用荷重		EA品番	コード No.
								(kgf)	(kN)		
LE-3M	2.6	9	17	31	30	M-3	4	15	0.15	EA638MD-3	315
LE-4M	3.5	10	20	40	38	M-4	8	20	0.20	EA638MD-4	316
LE-5M	4.3	13	26	52	47	M-5	15	30	0.29	EA638MD-5	317
LE-6M	5.2	16	30	60	56	M-6	25	50	0.49	EA638MD-6	318
LE-8M	7	18	36	60	55	M-8	50	80	0.78	EA638MD-8	319
LE-10M	8.6	24	44	80	75	M-10	103	150	1.47	EA638MD-10	320
LE-12M	10.5	29	55	100	97	M-12	184	220	2.16	EA638MD-12	321
LE-16M	14	38	70	145	127	M-16	441	450	4.41	EA638MD-16	810