



Artikel-Nr.	WLL in geradem Zug [t]	d1 [mm]	d2 [mm]	d3 [mm]	d4 [mm]	h [mm]	k [mm]	Gewicht [kg/100 Stk]
EA638SD-41	0,075	M 6	20	36	20	36	8	5,00
EA638SD-42	0,14	M 8	20	36	20	36	8	6,00
EA638SD-43	0,23	M 10	25	45	25	45	10	11,00
EA638SD-44	0,34	M 12	30	54	30	53	12	18,00
EA638SD-45	0,49	M 14	35	63	35	62	14	27,00
EA638SD-46	0,70	M 16	35	63	35	62	14	28,00
EA638SD-47	0,85	M 18	40	72	40	71	16	44,00
EA638SD-48	1,20	M 20	40	72	40	71	16	45,00
EA638SD-49	1,40	M 22	50	90	50	90	20	73,00

Artikel-Nr.	WLL in geradem Zug [t]	d1 [mm]	d2 [mm]	d3 [mm]	d4 [mm]	h [mm]	k [mm]	Gewicht [kg/100 Stk]
EA638SD-50	1,80	M 24	50	90	50	90	20	74,00
EA638SD-51	2,10	M 27	55	96	50	97	20	162,00
EA638SD-52	3,20	M 30	65	108	60	109	24	166,00
EA638SD-53	4,60	M 36	75	126	70	128	28	265,00
EA638SD-54	6,30	M 42	85	144	80	147	32	403,00
EA638SD-55	8,60	M 48	100	166	90	168	38	638,00
EA638SD-56	11,50	M 56	110	184	100	187	42	880,00
EA638SD-57	16,00	M 64	120	206	110	208	48	1,240,00