











Traglasten:

Tabelle 1:

Anschlagart												
kind of attachment												
Anzahl der Stränge		1	1	2	2	2	2	2	3 und 4	3 und 4	3 und 4	
number of strand												
Neigungswinkel		0°	90°	0°	90°	0°-45°	0°-60°	unsymm.	0°-45°	45°-60°	unsymm.	
angel of slope												
Artikelnummer	Gewinde	Gesamtgewicht "G" in Tonnen										
identification	thread	Gross weight "G" in tons										
EA638SR-21	66200060	M6	0,40	0,10	0,80	0,20	0,14	0,10	0,10	0,20	0,14	0,10
EA638SR-22	66200080	M8	0,80	0,20	1,60	0,40	0,28	0,20	0,20	0,40	0,28	0,20
EA638SR-23	66200100	M10	1,00	0,25	2,00	0,50	0,35	0,25	0,25	0,50	0,35	0,25
EA638SR-24	66200120	M12	1,60	0,40	3,20	0,80	0,56	0,40	0,40	0,80	0,56	0,40
EA638SR-25	66200160	M16	4,00	1,00	8,00	2,00	1,40	1,00	1,00	2,10	1,50	1,00
EA638SR-26	66200200	M20	6,00	1,50	12,00	3,00	2,10	1,50	1,50	3,00	2,10	1,50
EA638SR-27	66200240	M24	8,00	2,00	16,00	4,00	2,80	2,00	2,00	4,00	2,80	2,00
	66200270	M27	8,00	2,00	16,00	4,00	2,80	2,00	2,00	4,00	2,80	2,00
EA638SR-28	66200300	M30	12,00	3,00	24,00	6,00	4,20	3,00	3,00	6,00	4,20	3,00
EA638SR-29	66200360	M36	16,00	4,00	32,00	8,00	5,60	4,00	4,00	7,80	5,40	4,00
EA638SR-30	66200420	M42	24,00	6,00	48,00	12,00	8,40	6,00	6,00	11,80	8,20	6,00
EA638SR-31	66200480	M48	32,00	8,00	64,00	16,00	11,25	8,00	8,00	15,60	10,90	8,00