



Artikel-Nr.	WLL in geradem Zug [t]	d1 [mm]	d2 [mm]	d3 [mm]	d4 [mm]	h [mm]	k [mm]	Gewicht [kg/100 Stk]
67200060 EA638ST-1	0,40	M 6	20	36	20	36	8	5,00
67200080 EA638ST-2	0,80	M 8	20	36	20	36	8	6,00
67200100 EA638ST-3	1,00	M 10	25	45	25	45	10	11,00
67200120 EA638ST-4	1,60	M 12	30	54	30	53	12	18,00
67200160 EA638ST-5	4,00	M 16	35	63	35	62	14	28,00
67200200 EA638ST-6	6,00	M 20	35	72	40	71	16	45,00
67200240 EA638ST-7	8,00	M 24	50	90	50	90	20	72,00
67200300 EA638ST-8	12,00	M 30	65	108	60	109	24	166,00
67200360 EA638ST-9	16,00	M 36	75	126	70	128	28	265,00
67200420 EA638ST-10	24,00	M 42	85	144	80	147	32	400,00
67200480 EA638ST-11	32,00	M 48	100	166	90	168	38	658,00