

# Bessey catalog 2015/2016 Auto-Adjust toggle clamps

## Bessey Auto-Adjust Toggle Clamps Horizontal style, vertical flanged base



Bessey Product #	Opening	Opening	Holding capacity	Nominal Clamping Force		Case qty
				N	lbs. / kg	
STC-HV20	20	13/16	450	25-250	0.21	6



### Dimensions

No.	mm	Total Length	Length of extension arm	Spindle Adjustment range	Pressure plate diameter	Length of base	Length of base 1	Length of base 2	Length of composite handle	Overall Height (handle closed)	Height of handle (open)	Height of extension arm	Height of spindle (overall)	Height of base	Width of extension arm (external)	Width of extension arm (internal)	Width of composite handle	Width of base plate	Length of hole spacing 1	Length of hole spacing 2	Length of hole spacing 3	Width of elongated hole	Diameter of base mounting holes
		L1	L2	L3	L4	L5	L6	L7	L8	H1	H2	H3	H4	H5	B1	B2	B3	B4	Lo1	Lo2	Lo3	Lo4	e
STC-HV20	mm	167	45	20	16	83	38	-	46	65	162	10	42	45	10	6	20	18	10-13	26	13	-	5.6
	"	6.57	1.77	0.79	0.63	3.27	1.50	-	1.81	2.56	6.38	0.39	1.65	1.77	0.39	0.24	0.79	0.71	0.39-0.51	1.00	0.50	-	0.22

