

# Bessey catalog 2015/2016 Auto-Adjust toggle clamps

## Bessey Auto-Adjust Toggle Clamps Horizontal style, Inline, Face Mount, vertical flanged base



Bessey Product #	Opening mm	Opening "	Holding capacity N	Nominal Clamping Force lbs.	Weight kg	Case qty St.
STC-IHA15	10	3/8	450	25-250	0.23	6

### Dimensions

		Total Length	Length of extension arm	Spindle Adjustment range	Pressure plate diameter	Length of base	Length of base 1	Length of base 2	Length of composite handle	Overall Height (handle closed)	Height of handle (open)	Height of extension arm	Height of spindle (overall)	Height of base	Width of extension arm (external)	Width of extension arm (internal)	Width of composite handle	Width of base plate	Length of hole spacing 1	Length of hole spacing 2	Length of hole spacing 3	Width of elongated hole	Diameter of base mounting holes
No.		L1	L2	L3	L4	L5	L6	L7	L8	H1	H2	H3	H4	H5	B1	B2	B3	B4	Lo1	Lo2	Lo3	Lo4	ø
STC-IHA15	mm	181	-	-	16	105	-	-	46	81	149	-	-	63	8.5	-	20	45	26	20 - 26	26	-	5.6
	"	7.13	-	-	0.63	4.13	-	-	1.81	3.19	5.87	-	-	2.48	0.33	-	0.79	1.77	1.00	0.79 - 1.00	1.00	-	0.22

