

Depth and Angle Gauge

Single tool to measure both depths & angles

Head manufactured form selected steel with rust inhibiting black oxide finish

Head is graduated both on left and right to 15°, 30° and 45°

Steel rule is fitted to the head and can be locked in final position for depth or angular measurements by a knurled nut

## **ORDERING INFORMATION**

CAT NR.	ORD NR.	RULE LENGTH		BOX
		(INCH)	(MM)	QTY.
★ DG/6	01214	-	150	150
◆ DG/6/IN	01227	6	-	150





DG/6/IN