

# Operation Instruction

## A. Main Functions

1. Three function buttons: SET; UP; DOWN
2. Temperature Switch between: °C / °F
3. Temperature test range: 0°C -50°C
4. Sound for click
5. Power saving function
6. Voice control function
7. LED brightness adjustment:L—1,L—2,L—3
8. Resolution: 1°C ; update temperature: 60sec
9. Battery :4\*AAA (incl)

## B. Power-On

1. When Power-On→ LCD full display → enter the normal temperature state after "Beep"
2. Temperature scales defaults Celsius degree °C.

## C. Instruction of operating the Buttons

### 1. Normal states

- ✓ Press "SET" button to adjust the LED brightness
- ✓ Press "UP" to switch °C / °F display
- ✓ Press "DOWN" to select whether to turn on the power saving function (Turn on display " oNSd"; Turn off display "--Sd")

### 2. The function of Power saving

- ✓ When power on, the power saving Default power off (- -Sd), Press "DOWN" to turn on (oNSd) / off (-- sd) power saving mode.
- ✓ When turn on power saving, LED display automatically shut down if no key is operated in 30 seconds
- ✓ Enter power saving state, the system still keep the normal temperature

### 3. The function of Voice

- ✓ In the power saving state, Clap your hands or make a loud sound will turn on the LED display

- Messbereich 0°C ~ +50°C
- 3 Helligkeitsstufen einstellbar
- Inkl. Batterien (4x 1,5V AAAA)
- Inkl. USB-Ladekabel
- °C/°F-Anzeige

Drücken Sie die "SET"-Taste um die Helligkeit einzustellen. "L- 1, L- 2, L- 3" erscheint auf dem Display. Durch erneutes Drücken kann die Helligkeit verändert werden.

Drücken Sie die "UP"-Taste um zwischen °C und °F zu wählen.

Durch Drücken der "DOWN"-Taste können Sie den Energiesparmodus aktivieren ("oNSd" erscheint auf dem Display) bzw. deaktivieren ("--Sd" erscheint auf dem Display).

Ist der Energiesparmodus aktiviert, können Sie durch Bewegen des Geräts oder durch ein lautes Signal (z.B. Klatschen) in den normalen Anzeigemodus zurück gelangen.