


Specification of Low Pressure Gauge

株式会社 第一計器製作所
DAIICHI GAUGE MFG. CO., LTD.



大きさ SIZE	d	f	L	a	b	D	D1	h	H
60	G1/4B	14	14	8	36.5	73.5	65	59	96
	R1/4	14	14	8	36.5	73.5	65	59	96
75	G3/8B	18	17	11.5	43.5	83	75.5	69.5	111
	R3/8	15	17	11.5	43.5	83	75.5	66.5	108
100	G3/8B	20	22	15	47	108	99	86	140
	R3/8	18	22	15	47	108	99	84	138

③	Chamber チャンバー	C 5 1 9 1 P	Order No. 貴 注 番		
②	Socket 株	SUS 3 0 4	Scale Range 目盛範囲	k P a	
①	Case ケース	SUS 3 0 4	Quantity 台 数		
	Cover カバー	SUS 3 0 4	Remarks 備 考		
No.	Name 部品名	Material 材 質	Finish 処 理		
MATERIAL 材 質		DESIGNED FOR 品 名 Low Pressure Gauge B A N 微圧計		PLATES NO. 品 番	
FINISH 処 理		MODEL AND SIZE 型 名 A T $\phi 60$. $\phi 75$. $\phi 100$		DATE 2019. 02. 19	CHKD. KONTANI
SCALE 尺 度 Free		TOLERANCE 公 差 ±		DRWN. TANABE	APPD. TANABE
TITLE 図 名 Outside Drawing 外形図		DRWG NO. 図 番 B C 2 3 A T S 0 0 2 - 0 0 1			

