

PRODUCT DESCRIPTION:

- Sturdy aluminum housing
- 10W XPL CREE LED light
- Magnetic base holds to any ferrous metal surface
- Rotating head pivots to direct light to needed angle
- Includes 100-240V AC charger

BATTERY TREATMENT/CHARGING:

- Charge the battery for at least 8 hours before first use, but never charge over 10 hours
- Red indicator constant on: charging
- Green indicator constant on: charging completed
- Do not leave battery in full discharged condition
- Recharge the work light at least once every 30 days
- Do not turn ON the light during charging

SPECIFICATIONS:

Charger Specification:	100-240V AC / 50/60Hz
Charging Voltage/Current:	5V / 1000mA
Battery Specification:	3.6V / 2200mAh Li-ion rechargeable batteries
Time Of Charging:	approximately 5 hours
Time Of Discharging:	approximately 2.5 hours
Brightness:	750LM @ 45 meters

REPLACEMENT PARTS:

100-240V AC Charger

WARNING:

- *Green indicator constant on: charging completed*
- *Avoid looking directly into the beam*
- *Do not use the lamp near open flames*
- *Always fully charge to extend battery life*
- *Do not use this charger for any other products or any other charger for this product*

One year warranty from date of purchase from defects in materials.



Do not turn ON the light during recharging



All angle ball joint rotates to adjust work light beam to needed angle



10W CREE XPL high intensity LED light



Magnetic base mounts to any ferrous metal surfaces