

**Inspect, identify and repair with the Strion Switchblade. It's five lights in one: a droplight, hands-free light, UV light, bright white light and a high CRI light with Streamlight's Color-Rite Technology™.**

**You can work harder for longer with the PiggyBack® charger and easy-to-change battery - just twist off the endcap, replace and go.**



- Three operating modes:
- 90 CRI LEDs - Streamlight's Color-Rite Technology™ - to better see the color spectrum: 400 lumens; runs 3 hours
- UV LED for leak detection: 500mW; runs 5 hours
- Cool white LEDs for bright, white light: 500 lumens; runs 3 hours

High-impact, super-tough nylon polymer body with "Rocky Stipple" texture for a sure grip  
Machined aircraft aluminum light bar; chemical-resistant lens - withstands most common automotive chemicals

2m impact resistance tested

Folded length: 6" (15.24 cm); Extended length: 10.75" (27.30 cm)  
6.4 oz. (181g)

Limited Lifetime Warranty  
Visit [streamlight.com](http://streamlight.com) for full warranty information

- #74850 - Strion Switchblade - with USB cord - Red
- #74851 - Strion Switchblade - 120V/100V AC 1 holder - Red
- #74854 - Strion Switchblade - 120V/100V AC PiggyBack - Red
- #74852 - Strion Switchblade - 230V AC 1 holder - Red
- #74853 - Strion Switchblade - 240V UK/AUS AC 1 holder - Red