

Five lights in one: It's a droplight, a hands-free light, a bright white light, a high CRI light with Streamlight's Color-Rite Technology™ and it's a UV light. Features stronger magnet and robust hang hook.



|   |
|---|
| <ul style="list-style-type: none"> <li>- Three operating modes:</li> <li>- 90 CRI LEDs - Streamlight's Color-Rite Technology™ - to better see the color spectrum: 600 lumens; runs 3.75 hours</li> <li>- UV LED for leak detection: 500mW; runs 15 hours</li> <li>- Cool white LEDs for bright, white light: 800 lumens; runs 3.75 hours</li> </ul> |
| <p>High-impact, super-tough nylon polymer body with "Rocky Stipple" texture for a sure grip<br/>         Machined aircraft aluminum light bar; chemical-resistant lens</p>  |
| <p>IPX4 water resistant; 1m impact resistance tested</p>  |

|   |
|---|
| <p>Folded length: 9.8" (24.89 cm); Extended length: 17" (43.18 cm)<br/>         17.1 oz. (485g)</p>   |
| <p>Limited Lifetime Warranty<br/>         Visit <a href="http://streamlight.com">streamlight.com</a> for full warranty information</p>  |
| <p>#76802 - Stinger Switchblade - 230V AC 1 holder - Red<br/>         #76803 - Stinger Switchblade - 240V UK/AUS AC 1 holder - Red<br/> <b>#76801</b> - Stinger Switchblade - 120V/100V AC 1 holder - Red<br/>         #76800 - Stinger Switchblade - with USB cord - Red</p> |