

PRODUCT FACT SHEET

STINGER SWITCHBLADE® LED RECHARGEABLE AREA LIGHT

MARKET

APPLICATIONS: Law Enforcement, Sporting Goods, Security, Fire & Rescue, Hardware/Tool, Automotive, Industrial, Consumer

DESCRIPTION: Compact & extremely powerful, the Stinger Switchblade® LED rechargeable area light offers three (3) lighting

options. Cool white LEDs for area lighting. 90 CRI LEDs for color matching, and a UV LED for leak detection. All use the latest in power LED technology. The rechargeable battery results in one of the lowest operating costs of any area light of this type. The blade of the Switchblade can rotate 180° on the body. Soft detents will hold the blade in your desired position, and the light will stand on its tail with the light bar in any position. There are multiple ways to hook and hang the light. Use the hooks on the base plate or the retractable hook for many hanging options. The weighted base also includes magnets that will hold the light on any convenient

ferrous metal surface (in any orientation) to provide task-specific illumination.

CASE MATERIAL: Impact modified Nylon, non-slip textured barrel grip, and replaceable lenses.

DIMENSIONS: Stinger® Switchblade Length folded: 9.80 in. (24.89 cm) Diameter: Major Diameter: 1.62 in. (4.11 cm)

Length with the light bar fully extended: 17.0 in. (43.18 cm)

Body Diameter: 1.40 in. (3.56 cm)

WEIGHT: 17.1 oz (485 grams)

LENS: Lens is impervious to the most common automotive chemicals. Gasket sealed.

LIGHT SOURCE: 20 Cool White LEDs, 6000K, impervious to shock with a 50,000 hour lifetime.

20 90CRI Warm White LEDs, 4000K, impervious to shock with a 50,000 hour lifetime. One 400nm wavelength UV LED, impervious to shock with a 30,000 hour lifetime.

LIGHT OUTPUT: See Chart. Optimized electronics provides regulated intensity.

1800-LUMENS

ON/OFF: Easy access head mounted push-button switch. Depress the button momentarily to turn the light on. The Cool

white LEDs will come on and brighten in a few seconds. Press the button again and the cool white LEDs turn off and the 90 CRI color matching LEDs turn on. Press the button a third time and the 90 CRI LEDs turn off and

the UV LED turns on for leak detection. The fourth press will turn the light off.

RUN TIME:

3h 45min

See Chart.

BATTERY: Li Ion 5200 mAh cell.

CHARGING: Stinger® Smart Charger recharges light in 6.25 hours (5V/1A USB input) or 5 hours with 12VDC input.

NOTE- Light fits and charges in all existing Stinger® chargers. Charge times will vary.

USB charge port on the light using SL #22049, 22058, 22059, 22071, or 22072 charger, recharges in 8 hours.

FEATURES:

FLI STANDARD | FLI STANDARD | 1m |

LED technology for extreme brightness.

IPX4 Rated for water resistant operation.

1 meter impact resistance tested.

LED Charge-continuity indicator on charger base. Compact, snap-in charger mounts in any position.

Micro USB rechargeable.

WARRANTY: Streamlight's Limited Lifetime Warranty.

APPROVALS: CE Meets applicable European Community directives.

(BC) CEC Compliant

OPTIONAL

ACCESSORIES: None.

OUTPUT

RUN TIME

FL1 STANDARD	COOL WHITE	90 CRI	UV LED
314	800 LUMENS	600 LUMENS	500 mW
0	3h 45m	3h 45m	15h

^{*} With battery (included in purchase)

Issued: 10/16/2017

Revised: 04/17/2020 Rev: 7 Made in China Document #311