

Inspect, identify and repair with the Syclone.

It produces bright white light for everyday use or high CRI light with Streamlight's Color-Rite Technology™ for paint matching or identifying color differences in wires. Ultra-compact design doesn't get in the way and fits in small spaces.

Go hands-free with the flat, magnetic base and stowable hook.



Operating modes:

- Spot with cool white LED provides bright white light
 - » High: 400 lumens; 141m beam; runs 2 hours
 - » Medium: 200 lumens; 95m beam; runs 4.5 hours
 - » Low: 100 lumens; 72m beam; runs 9.5 hours
- Flood with 90 CRI LED using Streamlight's Color-Rite Technology™ for paint matching or to differentiate between wire colors:
 - » High: 300 lumens; 48m beam; runs 2 hours
 - » Medium: 150 lumens; 35m beam; runs 4 hours
 - » Low: 75 lumens; 24m beam; runs 8 hours

360° rotating body aims the beam where you need it; easy to rotate with one hand - no need to juggle tools

Tough thermoplastic construction; chemical-resistant lens

IPX4 water resistant; 2m impact resistance tested

2.97" (7.54 cm); 5.3 oz (150g)

Limited Lifetime Warranty

Visit streamlight.com for full warranty information

#61510 - Syclone - with USB cord - Box - Red