

Slim Worklight LED-370

360° Swivel









Super slim worklight for tight, cluttered and difficult to reach workspaces

Integrated

- a. 6W COB Worklight
- b. 1W Top Torch

User controlled output

Adjust light intensity from 0-600 lumen by rotating knob

Sturdy Construction

a. IP 54 Rated

Protected against dust and effects of water spray from any direction

b. IK 07 Rated

Impact proof ABS body

- Sturdy polycarbonate lens to withstand the toughest of job site conditions
- b. Nylon hook with ratcheting mechanism can be rotated full 360° for convenient placement of light as required

Swivel & tilt design

Patented 360° swivel & tilt mechanism.
Ball joint mechanism allows

- a. Swivelling of light full 360 $^{\circ}$
- b. Tilt

Hands Free Operation

Three rubber covered magnets at the rear end to affix light on any metallic surface leaving both hands free

Charging of Battery

Battery can be recharged using standard USB cable provided with the light

POWER SOURCE



3.7V 2600 mAh





	WORKLIGHT	TOP TORCH
INTENSITY	10	0%
LUMEN	600	120
RUN TIME	1.5 hours	10 hours

SWIVEL & TILT DESIGN



Patented 360° Swivel & tilt design with stainless steel joint




Rotating Hook with ratcheting mechanism

ORDERING INFORMATION

	CAT	ORD NR.	SIZE (L×H×D)		BOX
	NR.		(INCH)	(MM)	QTY.
	LED/370	55042	15-11/32 × 1-37/64 × 1-3/8	390 × 40 × 35	15

BRING IN THE LIGHT!









 ϵ

RoHs

IP54

IK07