Twin-Task® 3AA LED Flashlight

FL1 STANDARD	C4 LED	3-5mm LED
314	100 LUMENS	33 LUMENS
0	5h 45min	34h
	96m	43m
	2283cd	467cd



Case Material: Machined aluminum case with non-slip knurled grip and a matte black anodized finish

Dimensions: Length: 8.54 in. (21.7 cm) Major Diameter: 1.33 in. (3.38 cm) Body Diameter: 0.79 in. (2.00 cm)

Weight: 6.91 oz (196 grams) with alkaline batteries (included with purchase)

Lens: Unbreakable polycarbonate lens

Light Source: C4® LED technology, impervious to shock with a 50,000 hour lifetime

Three (3) white ultra bright LEDs with 100,000 hour lifetime

On/Off: Push button switch – sequences through C4® power LED, Three ultra bright LEDs, C4 power LEDand Off

Battery: Three (3) "AA" size alkaline batteries

Features: IPX4 rated for water resistant operation. All openings o-ring sealed.

1 meter impact resistance tested

Approvals: Meets applicable European Community Directives

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs,

abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may

have other specific legal rights which vary by jurisdiction

Item	UPC	Part #
Twin-Task 3AA LED Bla	ck 080926-51038-8	51038



^{*} With batteries (Included in purchase) Made in China