

POCKET MATE® USB ULTRA-COMPACT, USB RECHARGEABLE HIGH-PERFORMANCE HANDS-FREE LIGHT

Carabiner shape hangs cleanly on key ring, zipper, etc.









Material/Lens Impact resistant polycarbonate and machined aluminum frame. Unbreakable polycarbonate lens.

Dims/Weight Length: 2.0 in. (5.1 cm) Body Diameter: 0.5 in. (1.27 cm) Weight: 0.5 oz (14.2 grams)

Light Source/

Bright white LED with high and low modes

Output

- High: 325 lumens; 1,450 candela; 76m beam; runs 20 minutes

- Low: 45 lumens; 200 candela; 28m beam; runs 1 hour

Switch

Multi-function push-button switch

Battery

Lithium polymer battery charges in 4 hours

Charge indicator: Red = charging Green = fully charged

Features

- IPX4 weather resistant; 1m impact resistance tested

Approvals

Most models meet applicable European Community Directives

Warranty

Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction. Visit streamlight.com for full warranty information.

Item	UPC	Part #
Pocket Mate USB - USB cord - Box - Silver	080926-73300-8	73300
Pocket Mate USB - USB cord - Box - Red	080926-73301-5	73301
Pocket Mate USB - USB cord - Box - Blue	080926-73302-2	73302
Pocket Mate USB - USB cord - Box - Pink	080926-73303-9	73303

	Item	UPC	Part #
	40" USB Cord	080926-22070-6	22070
	22" USB Cord	080926-22081-2	22081