



DUALIE® RECHARGEABLE INTRINSICALLY SAFE RECHARGEABLE MULTI-FUNCTION FLASHLIGHT



- Material/Lens** Impact and chemical resistant Engineered Polymer resin; gasket sealed and vented. Class I, Division 1 models Available in high visibility yellow or black
- Dims/Weight** 7in. (17.78 cm); Length w/Magnetic clip: 7.50 in. (19.05 cm); Body thickness: 1.06 in. (2.69 cm) Body Width: 1.52 in. (3.86 cm)
Face cap diameter: 1.86 in. (4.72 cm)
Standard clip: 6.8 oz. (193g) with AA alkaline batteries (included in purchase). 5.9 oz. (167g) with AA lithium batteries
Magnetic clip: 7.1 oz. (201g) with AA alkaline batteries, 6.2 oz. (176g) with AA lithium batteries.
- Light Source/ Output** Two White C4® LEDs, impervious to shock with a 50,000 hour lifetime. Spot function uses a smooth parabolic reflector that produces a tight beam with optimum peripheral illumination. Flood beam produces a soft, wide beam to illuminate your work area. Spot and flood beams intersect for an uninterrupted light pattern to eliminate blind spots
- Features two C4® LEDs and three output modes: spot, flood, spot/flood combo:
- Spot: 180 lumens; 11,500 candela; 171m beam distance; runs 7.25 hours
 - Flood: 105 lumens; 60 candela; 18m beam distance; runs 13.5 hours
 - Spot/flood combo: 275 lumens; runs 5.5 hours
- Switch** Opposing head switches for easy identification. Spot LED push button head switch provides one handed momentary or constant operation. Flood LED push button head switch provides on/off operation.
- Battery** One 2600 mAh lithium ion battery recharges within 8 hours
- Features**
- Rugged, integrated, snag-free clip conforms to body of light
 - IP67 rated; dust-tight; waterproof to 1m for 30 minutes; 2m impact resistance tested
 - One-handed operation of all lighting modes
 - Ergonomically designed for maximum hand comfort
 - Corrosion Proof
- Approvals** Class I, II, Division 1, Groups A, B, C, D, E, F, G; Class III; CL I, ZN 0, IIC; Exia; T-Code: T4.
Meets applicable European Community Directives
- Warranty** Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction. Visit streamlight.com for full warranty information. Visit streamlight.com for full warranty information.

Description	UPC	Part #
Dualie Rechargeable 120V/100V AC - Yellow - Box	080926-68732-5	68732
Dualie Rechargeable 120V/100V AC- Black - Box	080926-68733-2	68733
Dualie Rechargeable 12V DC Direct Wire - Yellow - Box	080926-68734-9	68734
Dualie Rechargeable 12V DC Direct Wire - Black - Box	080926-68735-6	68735
Dualie Rechargeable Light Only - Yellow - Box	080926-68730-1	68730
Dualie Rechargeable Light Only - Black - Box	080926-68731-8	68731

EA758SD-76

EA758SD-77