


**EA758SD-81**
**EA758SD-82**

- Material/Lens** Impact and chemical resistant Engineered Polymer resin; v-ring sealed and vented. Unbreakable polycarbonate facecap and side lens with scratch resistant coating. Class I, Division 1 models Available in high visibility yellow or black.
- Dims/Weight** Length: 6.10 in. (15.5 cm) Body Diameter: 0.87 in. (2.2 cm) Face cap diameter: 1.34 in. (3.4 cm)  
3.9 oz. (111 grams) with AA alkaline batteries (included in purchase).
- Light Source/ Output** Two white LEDs, impervious to shock with a 50,000 hour lifetime. Spot function uses a smooth parabolic reflector that produces a tight beam with optimum peripheral illumination. Flood beam produces a soft, wide beam to illuminate your work area. Spot and flood beams intersect for an uninterrupted light pattern to eliminate blind spots
- Features two white LEDs and three output modes: spot, flood, spot/flood combo:
- Spot – 115 lumens, 3,100 candela peak beam intensity and 111 meter beam distance.
  - Flood – 115 lumens, 75 candela peak beam intensity and 17 meter beam distance.
  - Spot and Flood combined – 175 lumens
- Switch** Opposing head switches for easy identification. Spot LED push button head switch provides one handed momentary or constant operation. Flood LED push button head switch provides on/off operation.
- Battery** Two (2) "AA" size alkaline batteries. Mechanical battery polarity protection
- Features**
- IPx4 rated; 2m impact resistance tested
  - One-handed operation of all lighting modes
  - Removable and reversible belt/pocket clip
  - Corrosion Proof
- Approvals** Class I, II, Division 1, Groups A, B, C, D, E, F, G; Class III; CL I, ZN 0, IIC; Exia; T-Code: T4.  
II 1G Ex ia op is IIC T3/T4 Ga; FTZU 16ATEX0120X, IECEx FTZU 16.0022X  
Ex ia op is IIC T3/T4 Ga; DNV 17.0011X  
Meets applicable European Community Directives
- Warranty** Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction. Visit streamlight.com for full warranty information. Visit streamlight.com for full warranty information.

	Description	UPC	Part #
<b>EA758SD-81</b>	Dualie 2AA with two "AA" alkaline batteries. Clam - Yellow	080926-67750-0	67750
	Dualie 2AA with two "AA" alkaline batteries. Box - Yellow	080926-67751-7	67751
<b>EA758SD-82</b>	Dualie 2AA with two "AA" alkaline batteries. Clam - Black	080926-67752-4	67752
	Dualie 2AA with two "AA" alkaline batteries. Box - Black	080926-67753-1	67753