



EA758SE-46

STREAMLIGHT®

BANDIT® PRO

ULTRA-COMPACT, LOW-PROFILE
USB RECHARGEABLE HEADLAMP

The Bandit Pro is a long-running, low-profile headlamp that is USB rechargeable and provides 180 lumens of widespread white light for 4.5 hours.



<p>Three output modes: High, low and emergency flash</p> <ul style="list-style-type: none"> - High: 180 lumens; runs 4.5 hours - Low: 35 lumens; runs 21 hours - Emergency flash - flashes on high - 180 lumens
<p>Produces bright, even, diffused light with less shadow than spot beams</p> <p>Beam doesn't "bounce"</p> <p>Floods work area with light; Ideal for up-close tasks</p>
<p>Battery life indicator: with approx. 5 minutes of remaining run time, light enters a sequence of blinking three times and remaining on for 30 seconds until it shuts off</p>

<p>Impact-resistant polycarbonate construction</p> <p>IPX4 weather-resistant; 2m impact resistance tested</p>
<p>2.7" (6.85 cm); 1.6oz. (45.4g) with headband; 1.7 oz. (48.2g) with hat clip</p>
<p>Two Year Warranty</p> <p>Visit www.streamlight.com for full warranty information</p>
<p>#61711 Bandit Pro - USB cord, hat clip and elastic headstrap - Box - Yellow</p> <p>#61710 Bandit Pro - USB cord, hat clip and elastic headstrap - Clam - Yellow</p> <p>#61715 Bandit Pro - USB cord, hat clip and elastic headstrap - Box - Black</p> <p>#61714 Bandit Pro - USB cord, hat clip and elastic headstrap - Clam - Black</p> <p>#61716 Bandit Pro - elastic headstrap, rubber hard hat strap, 3M™ Dual Lock™ and USB cord - White LED - Yellow - Box</p>