

A low-profile headlamp with Class I, Div 1 safety ratings. Three lighting modes cover a variety of tasks: spot for a focused beam, flood for soft area illumination that won't tire your eyes and spot/flood combo for even more light output.



Spot/Flood Combo = 235 lumens


 Flood LED
 Spot LED


Lightweight, low-profile design



Includes rubber strap and 3M® Dual Lock® for strapless mounting to hard hats


Spot and flood beams:

- Spot: 160 lumens; 1,320 candela; 73m beam; runs 5 hours
- Flood: 160 lumens; 100 candela; 20m beam; runs 5 hours
- Spot/flood combo: 235 lumens; runs 4.75 hours

45° tilting head

Tough, polycarbonate thermoplastic construction with elastomer over mold; Unbreakable polycarbonate lenses; recessed to prevent scratches

IPX7 waterproof; 2m impact resistance tested

Class I, II, Division 1, Groups A, B, C, D, E, F, G; Class III; Class 1, Zone 0, Group IIC, Exia; T-Code: T4

MSHA Permissible Flashlight, Approval No. 20-A190001-0. Tested for Intrinsic Safety in Methane-Air mixtures only.

3.5 oz (99.2 grams) with batteries

Limited Lifetime Warranty
 Visit streamlight.com for full warranty information

#61424 - Enduro Pro - alkaline batteries, elastic headstrap, rubber hard hat strap, and 3M® Dual Lock® - Box - Yellow



ENDURO® PRO HAZ-LO® LOW PROFILE, SAFETY RATED MULTI-FUNCTION HEADLAMP



Includes rubber strap and 3M® Dual Lock® for strapless mounting to hard hats

Case Material/Lens Tough thermoplastic construction with elastomer over mold. Unbreakable polycarbonate lenses. Available in Safety Yellow.

Dims/Weight Height: 2.0 in. (5.08 cm) Width: 2.19 in. (5.68 cm) Depth: 1.5 in (3.81 cm)
3.5 oz (99.2 grams) with batteries.

Light Source Two white LEDs, impervious to shock with a 50,000 hour lifetime.

Output/Run Time Spot and flood beams:
Spot: 160 lumens; 1,320 candela; 73m beam; runs 5 hours
Flood: 160 lumens; 100 candela; 20m beam; runs 5 hours
Spot/flood combo: 235 lumens; runs 4.75 hours

Switch: Push button switch. Click the switch to step through each mode, Spot, Flood, Spot/Flood Combo, and OFF.

Battery Three "AAA" alkaline batteries (included). Mechanical battery polarity protected.

Features - IPX7 rated design; waterproof to 1meter for 30 minutes.
- 2m impact resistance tested
- 45° tilting head

Approvals Class I, II, Division 1, Groups A, B, C, D, E, F, G; Class III; Class 1, Zone 0, Group IIC, Exia; T-Code: T4 (approved for use with Energizer E92, Duracell MN2400, Rayovac NO.824, and Panasonic LR03PA).
MSHA Permissible Flashlight, Approval No. 20-A190001-0. Tested for Intrinsic Safety in Methane-Air mixtures only.
Meets applicable European Community directives.

Warranty Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction. Visit streamlight.com for full warranty information.

Item	UPC	Part #
Enduro Pro HAZ-LO - includes 3 AAA alkaline batteries, elastic headstrap, rubber hard hat strap, and 3M® Dual Lock® - Box - Yellow	080926-61424-6	61424
Enduro Pro Rubber Hard Hat Strap	080926-61426-8	61426

Made in China



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax • streamlight.com
©Streamlight, Inc. Enduro Pro HAZ-LO 5/19

3M® and Dual Lock® are registered Trademarks of the 3M Company