

FL 1 STANDARD	HIGH	MEDIUM	LOW
	1000 LUMENS	400 LUMENS	65 LUMENS
	1h 30min	2h 45min	20h
	232m	147m	60m
	13,500cd	5,400cd	900cd
	2m	2m	2m

Product is tested per ANSI/PLATO FL 1 - 2016 standard

ENGLISH

CAUTION:

The ProTac HL® USB Headlamp provides a powerful beam. When operated for a long time on high, it will get uncomfortably warm. This is NORMAL and is not a defect. Any LED headlamp of similar size and performance will produce similar amounts of heat during operation. The only way to reduce operating heat is to SIGNIFICANTLY lower the output, or increase the size of the headlamp. While this heating may trigger the drop reflex if an unattended hot light is picked up, the temperature does not present a burn hazard.

WARNING:

The ProTac HL® USB Headlamp utilizes a high lumen LED that can get very hot. Never place the ProTac HL® USB Headlamp face-down against a flat surface or against any flammable object. Transport or store the ProTac HL® USB Headlamp in a way that minimizes the chance it can accidentally be turned on.

BATTERY INSTALLATION/REMOVAL:

Remove the side switch cap. Place one Streamlight #74175 battery into the tube, positive end first and replace the switch cap.

The light will also function if you install one Streamlight #22101 "Li Ion 18650 protected cylindrical 3.7V 2600mAh 'button top' rechargeable battery" that has its own charging cradle system. NOTE -- This cell will not charge in the light.

GENERAL OPERATION:

The ProTac HL® USB Headlamp features a programmable switch with momentary operation (light press or tap) and constant on operation (press until click). The light is shipped from the factory in the default High-Medium-Low program.

- High: Tap and hold; click to lock on; click again for off.
- Medium: Fast double-tap (within 0.4 seconds) and hold; click to lock on; click again for off.
- Low: Fast triple-tap (within 0.4 seconds per tap) and hold; click to lock on; click again for off.

ACCESSING OTHER PROGRAMS:

The ProTac HL® USB Headlamp features a TEN-TAP® programmable switch allowing the user to select one of three different programs. To change to the next program, starting from the "Off" position, tap the switch rapidly 9 times (within 0.4 seconds per tap) and hold it down the 10th time. Continue holding the switch until the light turns off (approximately 1 second), then release the switch. Available programs are High-Medium-Low (Factory Default), High Only or Low-Medium-High.

CHARGING THE STREAMLIGHT LITHIUM ION BATTERY:

To charge the included Streamlight lithium ion battery (Part #74175), pull the rubber plug from the micro USB port on the bottom of the light to expose the charge port and charge indicator LED.

Using the supplied cord, plug the micro USB connector into the mating socket on the light. Then, plug the standard USB connector into a USB port on your computer or other USB accessible port.

If you have Streamlight's optional USB/AC charger (#22071), plug the USB connector into the light and charge the light using AC power.

CHARGE INDICATION LED:

Light features a charge indicator LED:

- Red LED: Charging
- Green LED: Fully Charged

CHARGE TIME:

The light has a digital control circuit that prevents over-charging. The battery fully recharges in about 5 hours with the Streamlight AC/USB (#22071) charger and charges the battery in the light.

NOTE: The 5 hour charge time assumes 1,000 mA output of the AC/USB charger. (Most computer USB power ports range from 100 to 500 mA.)

Streamlight's Limited Lifetime Warranty

Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase.

THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW.

You may have other specific legal rights which vary by jurisdiction. Go to www.streamlight.com/support for a

complete copy of the warranty and information on product registration and the location of authorized service centers. Retain your receipt for proof of purchase.

MAINTENANCE AND SERVICE

It is important to keep the O-ring on the switch cap lubricated.

Streamlight recommends the factory or authorized service centers for any repairs.

Customer Service
STREAMLIGHT, INC.
30 Eagleville Road
Suite 100

Eagleville, PA U.S.A. 19403-3996
Phone: (800) 523-7488 Toll-Free
Fax: (800) 220-7007
www.streamlight.com

ESPAÑOL

PRECAUCIÓN:

El faro USB ProTac HL® proporciona un potente haz. Cuando funciona durante un período prolongado en modo alto, alcanzará una temperatura caliente que resulta incómoda. Esto es NORMAL y no se trata de un defecto. Cualquier faro LED de tamaño y rendimiento similares producirá cantidades similares de calor durante el funcionamiento. La única manera de reducir el calor producido durante el funcionamiento consiste en disminuir de manera SIGNIFICATIVA la potencia o aumentar el tamaño del faro. Si bien este calor podría provocar el reflejo de dejarla caer, si se recoge una linterna caliente desatendida, la temperatura no presenta un riesgo de quemaduras.

ADVERTENCIA:

El faro USB ProTac HL® utiliza un LED de lumen alto que puede alcanzar una temperatura muy alta. No ponga nunca el faro USB ProTac HL® boca abajo contra una superfi-