

STYLUS PRO® USB UV

RECHARGEABLE UV PENLIGHT





Case Material/Lens: Anodized aluminum construction. Gasket sealed glass lens

Dimensions/Weight: Length: 6.15 in. (156 mm) Body Diameter: 0.74 in. (19 mm); 1.9 oz (53.8 grams) with battery

Light Source: 400 nanometer UV LED, impervious to shock with a 30,000 hour lifetime

Output/Run time: 325 mW measured system output; runs 2.5 hours

Fully regulated output for consistent UV performance over the battery life

On/Off: Push button tail switch - momentary or constant on operation

Battery/Charging: Lithium ion battery rechargeable up to 300 times; fully charges in 2.5 hours

Charges via USB port or AC wall adapter or DC cigarette adapter Charge indication LED: LED Red – Charging; LED Green – Charged

Features: • Removeable pocket clip

· O ring sealed, sliding cover protects the micro USB charging port

IPX4 water-resistant; 1 meter impact resistance tested

Approvals: Most models meet applicable European Community Directives

) CEC compliant

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also

excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.



Item Description	UPC	Part #
Stylus Pro USB UV with 120V AC adapter, USB cord, nylon holster	080926-66148-6	66148
Stylus Pro USB UV with USB cord, nylon holster	080926-66149-3	66149
Stylus Pro USB UV with International AC adapter, USB cord, nylon holster	080926-66150-9	66150
Stylus Pro USB Battery	080926-66143-1	66143
USB cord	080926-22070-6	22070
120V AC USB Cord	080926-22071-3	22071
International Wall Adapter	080926-22059-1	22059
12V DC USB Adapter	080926-22069-0	22069
EPU-5200	080926-22600-5	22600
Nylon Holster	080926-66029-8	66029





