

Our popular MicroStream is now available in a rechargeable model. Ultra-compact, this personal light, which fits in the palm of your hand or comfortably in your pocket, provides unparalleled performance for its size.

Removable, multi-directional pocket clip

Multi-function push-button tail switch

Durable, anodized machined aircraft aluminum construction

Lithium ion battery recharges in 4 hours

Unbreakable polycarbonate lens

Sliding metal sleeve protects USB port

Pocket clip attaches to visor for hands-free use



White LED with high and low modes: - High: 250 lumens; 1,150 candela; 68m beam distance; runs 1.5 hours - Low: 50 lumens; 250 candela; 31m beam; runs 3.5 hours
Lithium ion battery recharges in 4 hours Charge indicator: - Lights red when charging - Lights green when fully charge
Fully regulated output for consistent lumen performance over the battery life
IPX4 water-resistant; 1 meter impact resistance tested

3.87" (98.2 mm); 1.2 oz. (34.1g) with battery  Limited Lifetime Warranty Visit <a href="http://www.streamlight.com">www.streamlight.com</a> for full warranty information
#66601 - MicroStream USB with 5" USB cord and lanyard - Clam - Black #66604 - MicroStream USB with 5" USB cord and lanyard - Box - Black #66602 - MicroStream USB with 5" USB cord and lanyard - Clam - Red #66605 - MicroStream USB with 5" USB cord and lanyard - Box - Red #66603 - MicroStream USB with 5" USB cord and lanyard - Clam - Blue #66606 - MicroStream USB with 5" USB cord and lanyard - Box - Blue #66608 - MicroStream USB with 5" USB cord and lanyard - Clam - Coyote #66609 - MicroStream USB with 5" USB cord and lanyard - Box - Coyote #22600 - EPU-5200 Portable USB Charger



**MICROSTREAM USB®**  
**LITHIUM ION RECHARGEABLE FLASHLIGHT**

**MARKET**

**APPLICATIONS:** Professional Light - Hardware/Tool, Industrial, Law Enforcement, Security, Automotive, Sporting Goods, Consumer.

**DESCRIPTION:** The Microstream® USB is a compact Lithium ion battery powered flashlight designed for use in all markets. It features a tail cap switch, momentary or constant on operation, high and low beams, a combination pocket/hat clip for convenience, and amazing brightness and run time for a light of its size and price. The aluminum housing with Type II Military Spec anodizing helps make the light extremely durable and abrasion resistant. To charge the light, slide the head cover forward to expose the micro USB port.

**CASE MATERIAL:** Machined aluminum alloy case. Type II MIL-Spec anodized finish. Available in Black and Coyote.

**DIMENSIONS:** Length: 3.87 in. (98.2 mm) Body Diameter: 0.61 in. (15.6 mm)

**WEIGHT:** 1.20 oz. (34.1 grams) with battery (included with purchase).

**LENS:** Unbreakable polycarbonate lens.

**LIGHT SOURCE:** C4® LED technology, impervious to shock with a 30,000 hour lifetime.

**LIGHT OUTPUT:** High: 1150 candela peak beam intensity, 68 meter beam distance and 250 lumens measured system output.  
 Low: 250 candela peak beam intensity, 31 meter beam distance and 50 lumens measured system output.



**ON/OFF:** Push button tail switch - momentary or constant on operation.

**RUN TIME:** High: 1.5 hours of run time. Low 3.5 hours of run time. All runtime claims are to 10% of initial lumen output.



**BATTERY:** One (1) 350 mAh Streamlight Lithium Ion cell with on board safety circuit.

Fully recharges battery in 4.0 hours and charges battery in product.  
 Charge indication LED: Red - Charging; Green - Charged.

**FEATURES:**



C4® LED technology for extreme brightness.  
 IPX4 rated for water resistant operation. All openings o-ring sealed.  
 1 meter impact resistance tested.  
 Removable pocket/hat clip.

**APPROVALS:** Meets applicable European Community Directives.

CEC Compliant

**WARRANTY:** Streamlight's Limited Lifetime Warranty

**OPTIONAL**

**ACCESSORIES:** USB/AC adaptor(s).

	FL 1 STANDARD	HIGH	LOW
OUTPUT		250 LUMENS	50 LUMENS
RUNTIME		1.5h	3.5h
DISTANCE		68m	31m
INTENSITY		1,150cd	250cd

PERFORMANCE CURVE

