



## 2765

### Headlamp

Pelican™ safety approved headlamps are designed for use in hazardous environments. It is not only Class I Div 1 approved but also is ultra compact and lightweight. Equipped with three uniquely positioned LEDs, It produces up to 155 lumens and provides up to 8 hours of run time. The Pelican 2765 offers multiple modes (high, low, downcast, flashing). The downcast LEDs provides illumination for pathway (offering greater safety), reading space (added convenience) and most appreciated by your counterparts whenever face to face interaction is in order (no more blinding your partner). Additionally, the Pelican 2765 offers a full time battery level indicator. You will now be able to monitor your battery level throughout the life of the batteries. It is available in two colors (yellow or black). Count on Pelican to bring you the best in lighting design and technology.

The new Pelican™ 2765 headlamp: Guiding you safely through the danger zone.

- Built Pelican tough
- Hands-free design
- Night vision friendly
- Comfortable Cloth Strap
- Safety Certified - Class I, Division I



#### DIMENSIONS

**Length** 2.25" (5.7 cm)

#### MATERIALS

**Body** Polycarbonate (PC)  
**O-Ring** Over-molded TPR  
**Lens** Polycarbonate (PC)  
**Shroud** Polycarbonate (PC)

#### COLORS

High Visibility Yellow  Black

#### LIGHT SPECS

**Lamp Type** LED

#### POWER

**Battery Size** AAA  
**Battery Type** Alkaline  
**Battery Quantity** 3  
**Batteries Included** yes  
**Battery Level Indicator** Full-time battery indicator  
**Volts** 4.5v

#### WEIGHT







**Weight With Batteries** 3.4 oz (96 gr)  
**Weight Without Batteries** 2.1 oz (60 gr)

#### SWITCH

**Switch Type** Push Button  
**Light Modes** High / Low / Downcast / Flashing

#### CERTIFICATIONS

Class I, Division 1  
IECEX ia

FL1 STANDARD	DOWNCAST	MAIN & DOWNCAST HIGH	MAIN & DOWNCAST LOW	MAIN HIGH
	34 LUMENS	132 LUMENS	78 LUMENS	155 LUMENS
	14h 0mins	5h 30mins	8h 0mins	6h 15mins
	10m	68m	46m	81m
	23cd	1157cd	529cd	1649cd
	1m			
	IP54			