



2785

Headlamp

At long last, a high performance / long run time safety certified headlamp! The Class I, Division 1 / IECEx certified 2785 provides a Main, Downcast, Flashing, and combination LED modes. The focused Main LED provides a great distance beam while the Downcast LED projects a dispersed beam set at a 45° downward angle. This "Downcast" beam offers a number of benefits including safer illuminated pathways, reading capability, as well as convenient face to face applications. Options are plentiful as each mode is provided in an easy to select high, medium or low setting. The rear mounted battery pack is equipped with a full time battery level indicator in addition to a rear facing red LED for added safety. With over 200 lumens of high intensity light output available, coupled with the ability to last up to 100 hours in the low setting, the 2785 will support virtually all your hands free lighting needs. All this in a product that carries intrinsically safe certifications.

- 4 AA Batteries Included
- Pivoting Head For Directional Beam (60°)
- Rear Mounted Red LED
- Dual Beams including Downcast LED Technology
- 3 Light Levels
- Full Time Battery Level Indication
- Cloth and Rubber Straps Included



DIMENSIONS

Length	3.00" (7.6 cm)
---------------	----------------

MATERIALS

Body	Polycarbonate (PC)
O-Ring	Gasket
Lens	Polycarbonate (PC)
Shroud	Polycarbonate (PC)

COLORS

 Black	 High Visibility Yellow
---	--

LIGHT SPECS

Lamp Type	LED
Lamp Secondary Type	LED

POWER

Battery Size	AA
Battery Type	Alkaline
Battery Quantity	4
Batteries Included	yes
Battery Level Indicator	3 Blue LEDs
Volts	6.0v

WEIGHT

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311

Pelican

Weight With Batteries 8.8 oz (249 gr)

Weight Without Batteries 6.6 oz (187 gr)

sales@pelican.com • www.pelican.com






Document created on 05-13-24

SWITCH

Switch Type	Rotary / Push Button
Light Modes	High / Medium / Low / Downcast / Spot / Flashing

CERTIFICATIONS

Class I, Division 1
IECEX ia

FL1 STANDARD	MAIN HIGH	MAIN MED	MAIN LOW
	215 LUMENS	106 LUMENS	22 LUMENS
	5h 0mins	13h 0mins	98h 0mins
	108m	76m	34m
	2911cd	1445cd	290cd
	IP54		

ACCESSORIES