

EA758ZY-0.1～-15(φ6.4×30mm)(10本セット)
EA758ZZ-0.1～-15(φ6.4×30mm)(10本セット)



品番	定格電圧(V)	定格電流(A)
EA758ZY-0.1	125	0.1
EA758ZY-0.2		0.2
EA758ZY-0.3		0.3
EA758ZY-0.4		0.4
EA758ZY-0.5		0.5
EA758ZY-0.6		0.6
EA758ZY-0.8		0.8
EA758ZY-1		1
EA758ZY-1.5		1.5
EA758ZY-2		2
EA758ZY-3		3
EA758ZY-4		4
EA758ZY-5		5
EA758ZY-6		6
EA758ZY-7		7
EA758ZY-8		8
EA758ZY-10	10	
EA758ZY-12	12	
EA758ZY-15	15	

品番	定格電圧(V)	定格電流(A)
EA758ZZ-0.1	250	0.1
EA758ZZ-0.2		0.2
EA758ZZ-0.3		0.3
EA758ZZ-0.4		0.4
EA758ZZ-0.5		0.5
EA758ZZ-0.6		0.6
EA758ZZ-0.8		0.8
EA758ZZ-1		1
EA758ZZ-1.5		1.5
EA758ZZ-2		2
EA758ZZ-3		3
EA758ZZ-4		4
EA758ZZ-5		5
EA758ZZ-6		6
EA758ZZ-7		7
EA758ZZ-8		8
EA758ZZ-10	10	
EA758ZZ-12	12	
EA758ZZ-15	15	

- 電気的特性…普通溶断型(B種)
- 過電流・短絡電流の発生時、普通の時間で溶断します。
- 温度上昇…115% 100℃以下
- 通電…130%
- 溶断…160% 1時間以内
200% 2分以内
- 保管温度…-30～40℃
- 使用温度範囲…-20～80℃
- 使用湿度範囲…35～85%RH