
# **Laserliner**®

## **DampCheck**







- Checks the degree of dryness in firewood to conserve energy and reduce emissions.
- For checking the moisture content in soft building materials
- Measures the **ambient temperature**
- Numeric measured value display
- LED wet/dry indicator: 3 colour LEDs (green = dry, yellow = moist, red = wet) provide immediate measurement results for moisture content in the tested material.
- Switch between wood and building materials
- Hold function to retain the current measured value on the display
- Measured value display can switch between
  \*C and \*F

### **TECHNICAL DATA**

#### **MEASURING PRINCIPLE**

Resistive material moisture measurement by way of integrated electrodes

**MEASUREMENT RANGE / ACCURACY** 

(relative material moisture) WOOD ± 2% (6 ... 60%) BUILDING MATERIALS

± 0.5% (0.2 ... 2,9%)

**TEMPERATURE**  $\pm$  2 °C (0 ... 40 °C)

**STORAGE TEMPERATURE** -10 °C ... 50 °C **OPERATING TEMPERATURE** 0 ... 40 °C

MAX. RELATIVE HUMIDITY 85%

POWER SUPPLY


4 x LR44 button cell, 1.5 V

**DIMENSIONS** (W x H x D)

46 x 85 x 16 mm

WEIGHT (incl. batteries)

41 g



ARTICLE	ARTICLE NO	EAN-CODE	PU
DampCheck	082.003A	4 021563 689996	-





### DampCheck

- + protective cover
- + protective of + batteries

Packing dimension (W x H x D) 110 x 235 x 30 mm