



90 Degree Fixed Magnetic Clamps

- Fast, cost effective clamping of components rigid at 90° angles
- Ideal for weld preparation, fabrication and assembly of large components
- For jiggling on sheets, pipes and tubes
- 2 magnetic faces provide 90° clamping
- Angular tolerance: +/- 0.05/100mm

| Product Number | Length (mm) | Length (in) | Width (mm) | Height (mm) | Weight (kg) | Pull Force (kg) |
|------------------------|-------------|-------------|------------|-------------|-------------|-----------------|
| E971 EA781BK-11 | 140 | 5.51 | 35 | 140 | 1.4 | 40 |
| E972 EA781BK-12 | 225 | 8.86 | 22 | 225 | 2.2 | 75 |
| E973 EA781BK-13 | 300 | 11.81 | 35 | 300 | 4.7 | 200 |