

Heavy Duty Variable Magnetic Clamp



- Ideal for welding, fabrication and assembly of large components
- Powerful ferrite magnet material gives 40kg of clamping force
- Ideal for angles from 45 to 90°
- Marked at 15° increments to aid positioning
- Non-magnetic case stops attraction of stray ferrous materials

Looking for ultra-precise magnetic chucks see our [Workholding range](#).

Product Number	Length (mm)	Length (in)	Width (mm)	Height (mm)
E974 EA781BK-20	140	5.51	35	140