



Alnico Pocket Magnets

- 550° maximum operating temperature
- Alnico 5 magnet material
- Good corrosion resistance

Product Number	Length (mm)	Length (in)	Width (mm)	Height (mm)	Width of Gap (mm)	Weight per Pair (kg)	Pull Force (kg)
E802 EA781EA-11	28.5	0.874	7.6	25.4	6.3	0.03	2.4
E803 EA781EA-12	33.3	1.063	15.9	35	7.9	0.09	4