



Alnico Minor Magnets

- 550° maximum operating temperature
- Alnico 5 magnet material
- Good corrosion resistance

Product Number	Length (mm)	Length (in)	Width (mm)	Height (mm)	Pole Gap	Weight (kg)	Pull Force (kg)
E801 EA781EA-15	22.2	0.87	7.9	11.1	6.3	0.01	0.9