



Alnico Button Magnets

- 550° maximum operating temperature
- Alnico 5 magnet material
- Good corrosion resistance

Product Number	Length (mm)	Length (in)	Slot Size Min-Max (mm)	Hole Size	Weight (kg)	Pull Force (kg)		Dia. D (mm)
E821 EA781EA-21	9.5	0.37	4.0-7.2	4.4	0.006	0.7		12.7
E822 EA781EA-22	12.7	0.5	5.6-8.7	4.8	0.02	1.9		19.1
E825	19.1	0.75	6.3-6.3	4.8	0.05	3		22.2
E823 EA781EA-24	15.9	0.62	5.6-8.7	4.8	0.05	3.4		25.4
E824 EA781EA-25	25.4	1	8.0-12.7	7.1	0.113	4.8		31.8