



Alnico Power Magnets

- 550° maximum operating temperature
- Alnico 5 magnet material
- Good corrosion resistance

Product Number	Length (mm)	Length (in)	Width (mm)	Height (mm)	Width of Gap (mm)	Hole Size	Hole Centres	Weight (kg)	Weight per Pair (kg)	Pull Force (kg)
811 EA781EA-1	30	1.181	20	20	15	5	N/A	0.06	0.06	4.5
812 EA781EA-2	40	1.575	25	25	20	5	N/A	0.12	0.12	9
813 EA781EA-3	45	1.771	30	30	23	5	N/A	0.18	0.18	11.8
814 EA781EA-4	57	2.283	44.5	35	27.8	2 X 7.9	31.75	0.37	0.37	23.5
815 EA781EA-5	70	3.125	57.2	41.3	34.1	2 X 7.9	38.1	0.71	0.71	37
816 EA781EA-6	79.4	2.756	82.6	54	38.1	2 X 9.5	42.86	1.45	1.45	47
817 EA781EA-7	60.3	2.374	62	39.7	31.75	N/A	N/A	0.8	0.8	35
818 EA781EA-8	79.4	3.125	85.7	54	47.6	N/A	N/A	1.8	1.8	60