



Alnico Deep Pot Magnets

- 220° maximum operating temperature
- [Alnico 5](#) magnet material and mild steel pot
- Good corrosion resistance

Product Number	Height (mm)	Thread Size (mm)	Weight (kg)	Pull Force (kg)		Dia. D (mm)
829 EA781EB-1	15	M3	0.005	1		9.5
830 EA781EB-2	15.9	M4	0.015	2		12.7
831 EA781EB-3	16	M6	0.023	2.65		17.5
832 EA781EB-4	19	M6	0.04	4		20.5
833 EA781EB-5	25	M6	0.085	6.1		27
834 EA781EB-6	30	M6	0.184	14.75		35