



Alnico Cylindrical Bar Magnet

- 550° maximum operating temperature
- Alnico 5 magnet material
- Good corrosion resistance

Product Number	Length (mm)	Length (in)	Weight per Pair (kg)		Dia. D (mm)	Product Information	Gauss
E808 EA781EB-21	10	0.393	0.002		4	Supplied Natural	1200
E809 EA781EB-22	10	0.393			5	Supplied Natural	1200
E810 EA781EB-23	10	0.393			6	Supplied Natural	1200
E805 EA781EB-24	20	0.787	0.01		6		1200
E806 EA781EB-25	25	0.984	0.02		8		1200
E807 EA781EB-26	30	1.181	0.04		10		1200