



## Alnico Rectangular Bar Magnet

- 550° maximum operating temperature
- Alnico 2 or 5 magnet material
- Good corrosion resistance

Product Number	Length (mm)	Width (mm)	Height (mm)	Weight per Pair (kg)		Material	Gauss
E842 EA781EB-34	50	15	10	0.22		Alnico 2	750
E843 EA781EB-35	75	15	10	0.33		Alnico 2	750
E844 EA781EB-31	20	10	5	0.03		Alnico 5	1100
E845 EA781EB-32	40	12.5	5	0.04		Alnico 5	1100
E846 EA781EB-33	60	15	5	0.13		Alnico 5	1100