



## Alnico Shallow Pot Magnets

- 450° maximum operating temperature
- Alnico 5 magnet material and mild steel pot
- Good corrosion resistance

Product Number	Height (mm)	Hole Size	Screw Head Size	Weight (kg)	Pull Force (kg)		Dia. D (mm)
826 EA781EC-1	7.5	4.5	M3 CSK	0.01	3		19
827 EA781EC-2	8.5	5.2	M4 CSK	0.03	5		28.5
828 EA781EC-3	10.35	5.2	M4 CSK	0.08	13		38.1