



Ferrite Hook Magnets

- Supplied with removable threaded hook
- 120° maximum operating temperature
- Excellent resistance to corrosion
- Mild steel pot with white painted body

Pot Magnets with Hook / Ceiling Magnets

The pot magnets with a hook are sometimes called **ceiling magnets**. The pot magnets with a hook are white painted and are supplied with a detachable threaded hook.

The **ferrite** pot magnets with a hook have a maximum operating temperature of +120 degrees C. The **ferrite pot magnets with a hook** are cost effective magnets.

The **pot magnets with a hook** are widely used for hanging posters, banners and displays in supermarkets, large DIY stores, exhibition areas, car ferries and cruise ships.

Product Number	Pot Height (mm)	Total Height	Thread Size (mm)	Weight (kg)	Pull Force (kg)	Units per Pack	Dia. D (mm)
E879-RB EA781ED-11	8	34	M4	0.027	4	1	25
E880-RB EA781ED-12	8	34	M4	0.034	8	1	32
E881-RB EA781ED-13	8	34	M4	0.038	10	1	36