



Neodymium Shallow Pot Magnets-Thread Hole

- Strongest magnetic performance
- Zinc plated body
- N35 grade nickel plated magnet material
- 80°C max operating temperature

Product Number	Dia. (ØD)	Pot Height (mm)	Total Height	Thread Size (mm)	Ferrule Outer Dia.	Weight (kg)	Pull Force (kg)		Dia. D (mm)
E770NEO EA781EE-11	6	4.5	11.5	M3	6	0.0027	0.5		6
E771NEO	8	4.5	11.5	M3	6	0.0035	1.3		8
E772NEO EA781EE-13	10	4.5	11.5	M3	6	0.0045	2.5		10
E773NEO EA781EE-14	13	4.5	11.5	M3	6	0.0075	6		13
E774NEO	16	4.5	11.5	M4	8	0.0132	9.5		16
E775NEO EA781EE-16	20	6	13	M4	8	0.0165	14		20
E776NEO	25	7	14	M4	8	0.034	20		25
E777NEO EA781EE-18	32	7	15.5	M5	10	0.048	35		32