



Neodymium Deep Pot Bi-Pole Magnets-Threaded Hole

- Aluminium pot with mild steel pole pieces
- N35 grade nickel plated magnet material
- 80°C max operating temperature
- Ideal for clamping applications

Product Number	Height (mm)	Thread Size (mm)	Weight (kg)	Pull Force (kg)		Dia. D (mm)
NH025 EA781EE-21	12	M5	0.01	2.5		12.7
NH065 EA781EE-22	16	M6	0.018	8		16
NH130 EA781EE-23	20	M6	0.04	16		22.2
NH240 EA781EE-24	25	M6	0.07	25		25.4